



CWC Series Miniature Contactors

The CWC series mini contactors are a complete solution for switching and controlling motors. The CWC's compact dimensions for its IEC current rating, up to 22A, AC-3 utilization category, allows it to take up less space inside electrical enclosures while still maintaining a powerful 15 hp @ 460V. Dimensions of the 7A to 16A contactors are the same for both AC or DC coil voltages, making the panel design and assembly easier. DC models feature low consumption coils allowing the CWC to be operated directly from a PLC without interface relays.

Features

- Rated up to 15 hp @ 460V
- Direct mounting to the WEG RW17D overload relay
- Frame size is identical for AC and DC coil contactors up to 16A (CWC07-16).
- CWC025 frame available with AC coil only
- Heavy-duty operation
- Tool-free DIN-rail mounting
- WEG 18-month warranty
- Snap-on accessories
- DC coil low consumption: 1.7–2.7 W
- DC coil standard consumption: 2.6–3.7 W

Agency Approvals/ Certifications

- cULus listed (File No. E202315/E189202)
- CE marked low voltage directive 2006/95/EC

Standards

- IEC/EN 60947-1
- UL 508
- CSA-C22.2 No. 14




More Horsepower in a Smaller Frame



WEG CWC Series Miniature Contactors

Overview



- ① **Mini contactors**
– CWC07...16
- ② **Auxiliary frontal contact block**
– BFC0, BFC4
- ③ **Mechanical interlock block or latch block with connecting clips included**
– BIC0 (for use with CWC07...16)
– RMC0 (for use with CWC07...16)
- ④ **Surge suppressor blocks**
– RCC0, VRC0, DIC0
- ⑤ **Electronic Timers**
– TETC0 (for use with CWC07...25)
- ⑥ **Mini contactor**
– CWC025
- ⑦ **Auxiliary frontal contact block**
– BFC025
- ⑧ **Overload relay**
– RW17-2D (for use with CWC025)
– RW17-1D (for use with CWC07...16)
- ⑨ **Surge suppressor blocks**
– RCC0, VRC0

CWC Series Miniature Contactors Configuration

Three-Pole Contactors

Three-Pole Mini Contactors with AC Coil (IEC/EN – 60947-1)													
Part Number	Price	Current Rating		Maximum Rated Operational Power kW [hp]						Number of Contacts			Coil Voltage and Frequency
		AC-3 (A)	AC-1 (A)	220V 230V	380V	400V 415V	440V	500V	660V 690V	Main	Built-in Aux Contacts		
											N.O.	N.C.	
CWC07-10-30V04		7	18	1.5 [2]	3 [4]	3 [4]	3.7 [5]	3.7 [5]	3 [4]	3	1	–	24 VAC 60 Hz
CWC07-10-30V18										3	1	–	120 VAC 60 Hz/110 VAC 50 Hz
CWC07-10-30V24										3	1	–	208-240 VAC 60 Hz
CWC07-10-30V47										3	1	–	480 VAC 60 Hz/400-415 VAC 50 Hz
CWC07-01-30V04										3	–	1	24 VAC 60 Hz
CWC07-01-30V18										3	–	1	120 VAC 60 Hz/110 VAC 50 Hz
CWC07-01-30V24										3	–	1	208-240 VAC 60 Hz
CWC07-01-30V47										3	–	1	480 VAC 60 Hz/400-415 VAC 50 Hz
CWC09-10-30V04		9	20	2.2 [3]	4 [5.4]	4 [5.4]	4.5 [6]	4.5 [6]	4 [5.4]	3	1	–	24 VAC 60 Hz
CWC09-10-30V18										3	1	–	120 VAC 60 Hz/110 VAC 50 Hz
CWC09-10-30V24										3	1	–	208-240 VAC 60 Hz
CWC09-10-30V47										3	1	–	480 VAC 60 Hz/400-415 VAC 50 Hz
CWC09-01-30V04										3	–	1	24 VAC 60 Hz
CWC09-01-30V18										3	–	1	120 VAC 60 Hz/110 VAC 50 Hz
CWC09-01-30V24										3	–	1	208-240 VAC 60 Hz
CWC09-01-30V47										3	–	1	480 VAC 60 Hz/400-415 VAC 50 Hz
CWC012-10-30V04		12	22	3 [4]	5.5 [7.5]	5.5 [7.5]	5.5 [7.5]	5.5 [7.5]	5.5 [7.5]	3	1	–	24 VAC 60 Hz
CWC012-10-30V18										3	1	–	120 VAC 60 Hz/110 VAC 50 Hz
CWC012-10-30V24										3	1	–	208-240 VAC 60 Hz
CWC012-10-30V47										3	1	–	480 VAC 60 Hz/400-415 VAC 50 Hz
CWC012-01-30V04										3	–	1	24 VAC 60 Hz
CWC012-01-30V18										3	–	1	120 VAC 60 Hz/110 VAC 50 Hz
CWC012-01-30V24										3	–	1	208-240 VAC 60 Hz
CWC012-01-30V47										3	–	1	480 VAC 60 Hz/400-415 VAC 50 Hz
CWC016-10-30V04		16	22	4 [5.4]	7.5 [10]	7.5 [10]	7.5 [10]	7.5 [10]	7.5 [10]	3	1	–	24 VAC 60 Hz
CWC016-10-30V18										3	1	–	120 VAC 60 Hz/110 VAC 50 Hz
CWC016-10-30V24										3	1	–	208-240 VAC 60 Hz
CWC016-10-30V47										3	1	–	480 VAC 60 Hz/400-415 VAC 50 Hz
CWC016-01-30V04										3	–	1	24 VAC 60 Hz
CWC016-01-30V18										3	–	1	120 VAC 60 Hz/110 VAC 50 Hz
CWC016-01-30V24										3	–	1	208-240 VAC 60 Hz
CWC016-01-30V47										3	–	1	480 VAC 60 Hz/400-415 VAC 50 Hz
CWC025-00-30V04		22	32	5.5 [7.5]	11 [15]	11 [15]	11 [15]	11 [15]	11 [15]	3	–	–	24 VAC 60 Hz
CWC025-00-30V18										3	–	–	120 VAC 60 Hz/110 VAC 50 Hz
CWC025-00-30V24										3	–	–	208-240 VAC 60 Hz
CWC025-00-30V47										3	–	–	480 VAC 60 Hz/400-415 VAC 50 Hz
Three-Pole Mini Contactors with DC Coil (IEC/EN – 60947-1)													
CWC07-10-30L02		7	18	1.5 [2]	3 [4]	3 [4]	3.7 [5]	3.7 [5]	3 [4]	3	1	–	12 VDC low consumption
CWC07-10-30L03										3	1	–	24 VDC low consumption
CWC07-01-30L02										3	–	1	12 VDC low consumption
CWC07-01-30L03										3	–	1	24 VDC low consumption
CWC09-10-30L02		9	20	2.2 [3]	4 [5.4]	4 [5.4]	4.5 [6]	4.5 [6]	4 [5.4]	3	1	–	12 VDC low consumption
CWC09-10-30L03										3	1	–	24 VDC low consumption
CWC09-01-30L02										3	–	1	12 VDC low consumption
CWC09-01-30L03										3	–	1	24 VDC low consumption
CWC012-10-30L02		12	22	3 [4]	5.5 [7.5]	5.5 [7.5]	5.5 [7.5]	5.5 [7.5]	5.5 [7.5]	3	1	–	12 VDC low consumption
CWC012-10-30L03										3	1	–	24 VDC low consumption
CWC012-01-30L02										3	–	1	12 VDC low consumption
CWC012-01-30L03										3	–	1	24 VDC low consumption
CWC016-10-30L02		16	22	4 [5.4]	7.5 [10]	7.5 [10]	7.5 [10]	7.5 [10]	7.5 [10]	3	1	–	12 VDC low consumption
CWC016-10-30L03										3	1	–	24 VDC low consumption
CWC016-01-30L02										3	–	1	12 VDC low consumption
CWC016-01-30L03										3	–	1	24 VDC low consumption

Note: Low consumption 12 VDC and 24 VDC contactors can only use 2-pole auxiliary contact blocks.




CWC Series Miniature Contactors Configuration

Four-Pole Contactors


Four-Pole Mini Contactors with AC Coil (IEC/EN – 60947-1)																				
Part Number	Price	Current Rating		Maximum Rated Operational Power KW [hp]						Number of Main Contacts		Coil Voltage and Frequency								
		AC-3 (A)	AC-1 (A)	230V 230V	380V	400V 415V	440V	500V	660V 690V	N.O.	N.C.									
CWC07-00-40V04		7	18	1.5 [2]	3 [4]	3 [4]	3.7 [5]	3.7 [5]	3 [4]	4	–	24 VAC 60 Hz								
CWC07-00-40V18										4	–	120 VAC 60 Hz 110 VAC 50 Hz								
CWC07-00-40V24										4	–	208-240 VAC 60 Hz								
CWC07-00-40V47										4	–	480 VAC 60 Hz 400-415 VAC 50 Hz								
CWC07-00-22V04										2	2	24 VAC 60 Hz								
CWC07-00-22V18										2	2	120 VAC 60 Hz 110 VAC 50 Hz								
CWC07-00-22V24										2	2	208-240 VAC 60 Hz								
CWC07-00-22V47										2	2	480 VAC 60 Hz 400-415 VAC 50 Hz								
CWC09-00-40V04										9	20	2.2 [3]	4 [5.4]	4 [5.4]	4.5 [6]	4.5 [6]	4 [5.4]	4	–	24 VAC 60 Hz
CWC09-00-40V18		4	–	120 VAC 60 Hz 110 VAC 50 Hz																
CWC09-00-40V24		4	–	208-240 VAC 60 Hz																
CWC09-00-40V47		4	–	480 VAC 60 Hz 400-415 VAC 50 Hz																
CWC09-00-22V04		2	2	24 VAC 60 Hz																
CWC09-00-22V18		2	2	120 VAC 60 Hz 110 VAC 50 Hz																
CWC09-00-22V24		2	2	208-240 VAC 60 Hz																
CWC016-00-40V04		16	22	4 [5.4]	7.5 [10]	7.5 [10]	7.5 [10]	7.5 [10]	7.5 [10]									4	–	24 VAC 60 Hz
CWC016-00-40V18																		4	–	120 VAC 60 Hz 110 VAC 50 Hz
CWC016-00-40V24										4	–	208-240 VAC 60 Hz								
CWC016-00-40V47										4	–	480 VAC 60 Hz 400-415 VAC 50 Hz								
CWC016-00-22V04										2	2	24 VAC 60 Hz								
CWC016-00-22V18										2	2	120 VAC 60 Hz 110 VAC 50 Hz								
CWC016-00-22V24										2	2	208-240 VAC 60 Hz								
CWC016-00-22V47										2	2	480 VAC 60 Hz 400-415 VAC 50 Hz								

Four-Pole Mini Contactors with DC Coil (IEC/EN – 60947-1)												
Part Number	Price	Current Rating		Maximum Rated Operational Power KW [hp]						Number of Main Contacts		Coil Voltage and Frequency
		AC-3 (A)	AC-1 (A)	230V 230V	380V	400V 415V	440V	500V	660V 690V	N.O.	N.C.	
CWC07-00-40L02		7	18	1.5 [2]	3 [4]	3 [4]	3.7 [5]	3.7 [5]	3 [4]	4	–	12 VDC Low consumption
CWC07-00-40L03										4	–	24 VDC Low consumption
CWC07-00-22R02										2	2	12 VDC Standard consumption
CWC07-00-22R03										2	2	24 VDC Standard consumption
CWC09-00-40L02		9	20	2.2 [3]	4 [5.4]	4 [5.4]	4.5 [6]	4.5 [6]	4 [5.4]	4	–	12 VDC Low consumption
CWC09-00-40L03										4	–	24 VDC Low consumption
CWC09-00-22R02										2	2	12 VDC Standard consumption
CWC09-00-22R03										2	2	24 VDC Standard consumption
CWC016-00-40L02		16	22	4 [5.4]	7.5 [10]	7.5 [10]	7.5 [10]	7.5 [10]	7.5 [10]	4	–	12VDC Low consumption
CWC016-00-40L03										4	–	24VDC Low consumption
CWC016-00-22R02										2	2	12VDC Standard consumption
CWC016-00-22R03										2	2	24VDC Standard consumption


Note: Low consumption 12VDC and 24VDC contactors can only use 2-pole auxiliary contact blocks.




CWC07-10...cwc016-10




CWC07-01...cwc016-01



CWC025-00




CWC07-00-40...cwc016-00-40



CWC07-00-22...cwc016-00-22

Weg CWC Series Miniature Contactors Configuration

How to Identify Your Part Number



MINIATURE CONTACTOR SERIES CWC


FRAME RATING	
07	7A
09	9A
012	12A
016	16A
025	22A

COIL VOLTAGE	
VAC COIL	
V04	24 VAC 60 Hz
V18	120 VAC 60 Hz
V24	208-240 VAC 60 Hz
V47	480 VAC 60 Hz
VDC Coil (std consumption)	
R02	12 VDC
R03	24 VDC
VDC Coil (low consumption)	
L02	12 VDC
L03	24 VDC

BUILT-IN AUXILIARY CONTACTS	
00	None
10	1 N.O. (13 – 14 N.O.)
01	1 N.C. (21 – 22 N.C.)

POWER POLE	
30	CWC0 with 3 N.O. Power Poles (L1/T1, L2/T2, L3/T3)
22	CWC0 with 2 N.O. + 2 N.C. Power Poles (L1/T1, L2/T2, L3/T3, L4/T4)
40	CWC0 with 4 N.O. Power Poles (L1/T1, L2/T2, L3/T3, L4/T4)

Note: For reference only. Not intended to build a part number.



CWC07-00-40...cwc016-00-40

CWC07-00-22...cwc016-00-22



CWC Series Miniature Contactors

Technical Characteristics

CWC Miniature Contactors General Technical Characteristics

Contactors Part Numbers			CWC07	CWC09	CWC012	CWC016	CWC025
Standards			IEC/EN 60947-1, IEC/EN 60947-4, DIN VDE 0660(102), UL 508				
Rated Insulation Voltage U_i (Pollution Degree 3)	IEC/EN 60947-4-1, VDE 0660	(V)	690				
	UL, CSA	(V)	600				
Rated Impulse Withstand Voltage U_{imp}	(IEC/EN 60947-1)	(kV)	4				
Rated Operational Frequency (Contact Switchable)		(Hz)	25-400				
Mechanical Lifespan	AC coil	Ops x 10 ⁶	10			3	
	DC coil	Ops x 10 ⁶	12			-	
Electrical Lifespan	I_e AC-3	Ops x 10 ⁶	1.4	1.3	1.2	1.1	0.6
Degree of Protection (VDE 0160)	Main circuits		IP20				
	Control circuits and auxiliary contacts		IP20				
Mounting			Screw or DIN-rail 35mm (EN 50022)				
Coil Terminals			2				
Vibration Resistance	Contactor open		2				
	Contactor closed		4				
Mechanical Shock Resistance (½ sinusoid = 11ms)	Contactor open		6				
	Contactor closed		10				
Ambient Temperature	Operation		-25 to +55 °C [-13 to +131 °F]				
	Storage		-55 to +80 °C [-67 to +176 °F]				
Maximum Operating Altitude (Without Derating)			Up to 3000m [9842.5ft]				
Altitude derating	0.72 x rated hp		3000 – 4000m [9842.5 – 13123.4ft]				
	0.60 x rated hp		4000 – 5000m [13123.4 – 16404.2ft]				

UL 508 and IEC/EN Specifications

Contactors part numbers			CWC07	CWC09	CWC012	CWC016	CWC025
Standards			UL 508/CSA Ratings				
Rated Operating Voltage		(V)	600				
UL General Purpose Rating		(A)	18	20	22	22	30
Switching Motor Loads Full Voltage		(Hz)	50/60				
1-phase	115V	(A)	7.2	7.2	9.8	16	20
	230V	(A)	6.9	8	12	12	17
	115V	(hp)	1/3	1/3	1/2	1	1-1/2
	230V	(hp)	3/4	1	2	2	3
3-phase	208V	(A)	6.9	7.8	11	11	17.5
	230V	(A)	6	9.6	9.6	15.2	22
	460V	(A)	7.6	7.6	11	14	21
	575V	(A)	6.1	9	9	11	17
	208V	(hp)	1-1/2	2	3	3	5
	230V	(hp)	1-1/2	3	3	5	7-1/2
	460V	(hp)	5	5	7-1/2	10	15
575V	(hp)	5	7-1/2	7-1/2	10	15	
Short Circuit Current Rating (SCCR)	600V	(kA)	5	5	5	5	5
Standards			IEC Ratings (IEC/EN 60947)				
Rated Operating Voltage		(V)	690				
Rated Thermal Current I_{th}	AC-1 (≤ 55 °C)	(A)	18	20	22	22	32
	AC-3 ($U_e \leq 440V$)	(A)	7	9	12	16	22
Switching Motor Loads		(Hz)	50/60				
3-phase	220-240V	(A)	7	9	12	16	22
	380-400V	(A)	7	9	12	16	22
	415-440V	(A)	7	9	12	16	22
	500V	(A)	6.2	7.5	8.8	13	16
	660-690V	(A)	4.5	5.5	6.6	10	13
	220-240V	(kW)	1.5	2.2	3	3.7	5.5
	380-400V	(kW)	3	3.7	5.5	7.5	11
	415-440V	(kW)	3.7	4.5	5.5	7.5	11
	500V	(kW)	3.7	4.5	5.5	7.5	11
	660-690V	(kW)	3	3.7	5.5	7.5	11



CWC Series Miniature Contactors

Technical Characteristics

Control Circuit - Alternating Current (AC)							
Contactor part numbers			CWC07	CWC09	CWC012	CWC016	CWC025
Rated Insulation Voltage U_i (Pollution Degree 3)	IEC/EN 60947-4-1, VDE 0660	(V)	1000				
	UL, CSA	(V)	600				
Coils Rated Voltage	50 Hz	(V)	10-550				
	60 Hz	(V)	12-660				
	50/60 Hz	(V)	12-660				
Coil operating limits							
Coil 60 Hz	Pick up percent of voltage	(%)	40-76				
	Drop out percent of voltage	(%)	25-65				
Coil 50/60 Hz	Pick up percent of voltage	(%)	50-80				
	Drop out percent of voltage	(%)	20-60				
Average consumption							
Coil 60 Hz	Magnetic circuit closed	(VA)	2.5-3.5			10.8-13.2	
	Power factor	(cos ϕ)	0.28			0.32	
	Power dissipation per pole	(W)	2.6			-	
	Magnetic circuit closing	(VA)	35			72	
	Power factor	(cos ϕ)	0.85			0.93	
Coil 50/60 Hz	Magnetic circuit closed	(VA)	2-3			4.56-5.8	
	Magnetic circuit closing	(VA)	30			58	
Average Time	Closing N.O. contacts	(ms)	8-20			13-16	
	Opening N.O. contacts	(ms)	6-13			13.5-17	

Control Circuit - Direct Current (DC)						
Contactor Part Numbers			CWC07, CWC09, CWC012, CWC016			
Coil Type			Standard	Low consumption	4P (2P/2R)	
Rated Insulation Voltage U_i (Pollution Degree 3)	IEC/EN 60947-4-1, VDE 0660	(V)	1000			
	UL, CSA	(V)	600			
Standard Voltages			(V) 12-440			
Coil operating limits						
Coil Operating Limits	Pick up percent of voltage	(%)	40-70			
	Drop out percent of voltage	(%)	15-40			
Power consumption						
Power Consumption	Magnetic circuit closed	(W)	2.6-3.7	1.7-2.7	2.9-4	
	Magnetic circuit closing	(W)	2.6-3.7	1.7-2.7	2.9-4	
Operation Time	Closing N.O. contacts	(ms)	35-45			
	Opening N.O. contacts	(ms)	7-12			



CWC Series Miniature Contactors

Technical Characteristics

CWC Series Miniature Contactors Power Circuit							
Contactor Part Numbers			CWC07	CWC09	CWC012	CWC016	CWC025
Rated Operational Current I_e	AC-3 ($U_e \leq 440V$)	(A)	7	9	12	16	22
	AC-4 ($U_e \leq 440V$)	(A)	2.8	3.5	4.5	5	9
	AC-1 ($\theta_m \leq 55^\circ C, U_e \leq 690V$)	(A)	18	20	22	22	32
Rated Operational Voltage U_e	IEC/EN 60947-4-1, VDE 0660	(V)	690				
	UL, CSA ¹	(V)	600				
Rated Thermal Current I_{th} ($\theta \leq 55^\circ C$)		(A)	18	20	22	22	32
Making capacity - IEC/EN 60947		(A)	70	90	120	160	250
Breaking Capacity IEC/EN 60947	($U_e \leq 400V$)	(A)	50	72	96	128	200
	($U_e = 500V$)	(A)	50	72	96	128	200
	($U_e = 690V$)	(A)	35	54	72	96	150
Short-time Current (No Current Flowing During Recovery Time of 10 min and $\theta \leq 40^\circ C$)	1s	(A)	250	250	250	250	-
	5s	(A)	125	125	125	125	-
	10s	(A)	95	95	95	95	-
	30s	(A)	70	70	70	70	-
	1 min	(A)	50	50	50	50	-
	3 min	(A)	40	40	40	40	-
Protection Against Short-Circuits With Fuses (IEC gL/gG) ² or UL Class CC	@ 600V - UL/CSA ¹	(kA)	5				
	Coordination type 1	(A)	35	35	35	35	50
	Coordination type 2	(A)	20	20	25	25	35
Average Impedance Per Pole		(m Ω)	6	6	5	5	6
Average Power Dissipation Per Pole	AC-1	(W)	1.9	2.4	2.4	2.4	6.1
	AC-3	(W)	0.3	0.5	0.7	1.3	3.8
Utilization Category AC-3							
Rated Operational Current I_e ($\theta \leq 55^\circ C$)	($U_e \leq 440V$)	(A)	7	9	12	16	22
	($U_e \leq 500V$)	(A)	6.2	7.5	8.8	13	16
	($U_e \leq 690V$)	(A)	4.5	5.5	6.6	10	13
	($U_e \leq 1000V$)	(A)	Not available				
Rated Operational Power	220/230V	(kW)	1.5	2.2	3	3.7	5.5
		(hp)	2	3	4	5	7.5
	380V	(kW)	3	3.7	5.5	7.5	11
		(hp)	4	5	7.5	10	15
	400/415V	(kW)	3	3.7	5.5	7.5	11
		(hp)	4	5	7.5	10	15
	440V	(kW)	3.7	4.5	5.5	7.5	11
		(hp)	5	6	7.5	10	15
	500V	(kW)	3.7	4.5	5.5	7.5	11
		(hp)	5	6	7.5	10	15
	660/690V	(kW)	3	3.7	5.5	7.5	11
		(hp)	4	5	7.5	10	15
Maximum Electrical Operations per Hour	600 ops/hr	(%)	100	100	100	100	100
	1200 ops/hr	(%)	75	75	75	75	75
	3000 ops/hr	(%)	50	50	50	50	50
Utilization Category AC-4							
Rated Operational Current I_e AC-4 ($U_e \leq 440V$)		(A)	2.8	3.5	4.5	5	9
Rated Operational Power (200,000 Operations)	220/230V	(kW)	0.55	0.75	0.75	1.1	2.2
		(hp)	0.7	1	1	1.5	2.9
	380/400V	(kW)	1.1	1.1	1.8	2.2	4
		(hp)	1.5	1.5	2.4	2.9	5.4
	415V	(kW)	1.1	1.5	2.2	2.2	4.5
		(hp)	1.5	2	2.9	2.9	6
	440V	(kW)	1.1	1.5	2.2	2.2	4.5
		(hp)	1.5	2	2.9	2.9	6
	500V	(kW)	1.1	1.5	2.2	2.2	4.5
		(hp)	1.5	2	2.9	2.9	6
	660/690V	(kW)	1.1	1.5	2.2	2.2	4.5
		(hp)	1.5	2	2.9	2.9	6

¹Note: Specifications only valid for 50/60 Hz three-phase, 4 poles WEG standard motors.

²Note: Not sold by Automation Direct.



CWC Series Miniature Contactors

Technical Characteristics


Built-In Auxiliary Contacts Technical Characteristics			
Standards	IEC 60947-5-1, IEC 60947-4-1		
Rated Insulation Voltage U_i (Pollution Degree 3)	IEC, VDE 0660	(V)	690
	UL, CSA	(V)	600
Rated Operational Voltage U_e	IEC, VDE 0660	(V)	690
	UL, CSA	(V)	600
Rated Thermal Current I_{th} ($\theta \leq 55^\circ\text{C}$)		(A)	10
Rated Operational Current I_e			
AC-15 (IEC 60947-5-1)	$U_e \leq 240\text{V}$	(A)	10
	380–400V	(A)	6
	415–440V	(A)	6
	500V	(A)	4
	660–690V	(A)	2
UL/CSA			A600
DC-13 (IEC 60947-5-1)	24V	(A)	6
	60V	(A)	2
	110V	(A)	1
	220–240V	(A)	0.3
UL/CSA			Q600
Making Capacity (rms)	U_e 400V 50/60 Hz - AC-15	(A)	$10 \times I_e$ (AC-15)
Breaking Capacity (rms)	U_e 400V 50/60 Hz - AC-15	(A)	$10 \times I_e$ (AC-15)
Maximum IEC Fuse Class gL/gG Without Welding (Short-Circuit Protection) gL/gG		(A)	10
Control Circuit Reliability		(V/mA)	17 / 5
Electrical Endurance	(Millions operations)		1
Mechanical Endurance	(Millions operations)		10




CWC Series Miniature Contactors

Electrical Durability

AC-3 ($U_e \leq 440 \text{ VAC}$)




AC-4 ($U_e \leq 440 \text{ VAC}$)




WEG CWC Series Miniature Contactors Dimensions

Dimensions


mm [inches]



CWC07, CWC09, CWC012, CWC016 + VRC0/RCC0/DIC0




CWC07-16 + bico/RMCO




CWC025

Mounting position for CWC miniature contactors



WEG CWC Series Miniature Contactors Accessories

Front Mounting Auxiliary Contact Blocks

Auxiliary Contact Blocks											
Use With	2 Maximum # of Contacts				Price	Use With	2 Maximum # of Contacts				
	Auxiliary Contacts		Terminal Markings	Part Number			Auxiliary Contacts		Terminal Markings	Part Number	Price
N.O.	N.C.	N.O.			N.C.	N.O.	N.C.				
Three-Pole Contactors (CWC07, CWC09, CWC012, CWC016)	2	0		BFC0-20*		Four-Pole Contactors (CWC07, CWC09, CWC016)	2	0		BFC4-20*	
	1	1		BFC0-11*			1	1		BFC4-11*	
	0	2		BFC0-02*			0	2		BFC4-02*	
	4 Maximum # of Contacts						4 Maximum # of Contacts				
	4	0		BFC0-40			4	0		BFC4-40	
	2	2		BFC0-22			2	2		BFC4-22	
	0	4		BFC0-04			0	4		BFC4-04	
3	1		BFC0-31		3	1		BFC4-31			
1	3		BFC0-13		1	3		BFC4-13			
Three-Pole Contactors CWC025	2 Maximum # of Contacts					*Note: Low consumption 12 VDC and 24 VDC contactors can only use 2-pole auxiliary contact blocks					
	2	0		BFC025-20		 BFC0-11					
	1	1		BFC025-11							
0	2		BFC025-02								

WEG CWC Series Miniature Contactors Accessories


Auxiliary Contact Blocks Technical Specifications

Auxiliary Contacts BFC0/BFC4/BFC025 Technical Specifications			
Standards	IEC 60947-5-1, IEC 60947-4-1		
Rated Insulation Voltage U_i (Pollution Degree 3)	IEC, VDE 0660	(V)	1000
	UL, CSA	(V)	600
Rated Operational Voltage U_e	IEC, VDE 0660	(V)	690
	UL, CSA	(V)	600
Rated Thermal Current I_{th} ($\theta \leq 55^\circ\text{C}$)		(A)	10
Making Capacity (rms)	U_e 400V 50/60 Hz - AC-15	(A)	30
Breaking Capacity (rms)	U_e 400V 50/60 Hz - AC-15	(A)	3
Maximum IEC Fuse Class gL/gG Without Welding (Short-Circuit Protection)		(A)	10
Minimum Switching Capacity		(V/mA)	17 / 5
Electrical Endurance	(Millions operations)		1
Mechanical Endurance	(Millions operations)		10

AC Auxiliary Contact Block Ratings UL/CSA											
Contact Rating Code Designation	Thermal Continuous Current (A)	Maximum Current (A)								Maximum Apparent Power (VA)	
		120V		240V		480V		600V			
		Make	Break	Make	Break	Make	Break	Make	Break	Make	Break
A600	10	60	6	30	3	15	1.5	12	1.2	7200	720
C600	2.5	15	1.5	7.5	0.75	3.75	0.375	3	0.3	1800	180

DC Auxiliary Contact Block Ratings UL/CSA				
Contact Rating Code Designation	Thermal Continuous Current (A)	Maximum Make or Break Current (A)		Maximum Make or Break Apparent Power (VA)
		125V	250V	
Q600	2.5	0.55	0.27	69
R300	1	0.22	0.11	28

Terminals Capacity and Tightening Torque – Power, Control Circuits, and Auxiliary Contact Blocks




Terminals Capacity and Tightening Torque - Power, Control Circuits and Auxiliary Contact Blocks						
Terminal Type		CWC07...16		CWC025		BFC0/BFC4/BFC025
		Main Contacts	Auxiliary Contacts	Main Contacts	Auxiliary Contacts	Auxiliary Contacts
Solid Cable	mm ²	1x 0.5–2.5	2x 0.5–2.5	1x 0.5–2.5	2x 0.5–2.5 1x 4	–
		2x 0.5–2.5		–		
Cable Without Ferrule	mm ²	1x 0.75–2.5	2x 0.5–2.6	2x 1–2.5	1x 0.75–2.5 2x 0.75–2.5	1x 0.75–4
		2x 0.75–2.5		2x 2.5–6		2x 0.75–2.5
Cable With Ferrule	mm ²	1x 2.5	–	2x 1–2.5	1x 0.5–2.5 2x 0.5–2.5	1x 0.5–4
		2x 2.5		2x 2.5–6		2x 0.5–2.5
Wire Gauge	AWG	1 or 2x 18–12	22–14	1 or 2x 18–10	22–14	22–14
Terminal Screws		M3 flat/philips	M3.5 flat/philips	M3 flat/philips	M3.5 flat/philips	M3.5 flat/philips
Tightening Torque	N·m [lb·in]	1–1.5 [8.85–13.28]	1–1.7 [8.85–15.05]	1.4–1.7 [12.39–15.05]	1–1.5 [8.85–13.28]	0.8–1.5 [7.08–13.28]

WEG CWC Series Miniature Contactors Accessories

Surge Suppressors

Surge Suppressors					
Part Number	Price	Circuit Diagram	Voltage	Max. Clamping Voltage @ Current (Ip)	For Use With
RCC0-1D49			12-24 VAC 50/60 Hz	N/A	RC Resistor/ Capacitor AC Loads (The capacitor is used to absorb the voltage spike)
RCC0-2D53			24-48 VAC 50/60 Hz		
RCC0-3D55			50-127 VAC 50/60 Hz		
RCC0-4D63			130-250 VAC 50/60 Hz		
RCC0-5D84			275-380 VAC 50/60 Hz		
RCC0-6D73			400-510 VAC 50/60 Hz		
VRC0-1E49			12-48 VAC 50/60 Hz 12-60 VDC	135V @ 10A	MOV Varistor AC or DC Loads The voltage surge is limited to 3 times the voltage rating of the suppressor (300% of the rated coil voltage). Clamps voltage
VRC0-2E34			50-127 VAC 50/60 Hz 60-180 VDC	395V @ 10A	
VRC0-3E50			130-250 VAC 50/60 Hz 180-300 VDC	710V @ 10A	
VRC0-5D73			400-510 VAC 50/60 Hz	775V @ 10A	
DICO-1C33			12-600 VDC (1N4007)	N/A	Diode DC Loads The diode allows the remanent current to flow from a DC coil very smoothly and avoids an increase in voltage through the coil. Flyback suppression



RCC0-5D84

Electronic Timing Relays

(CWC07...CWC025)


Star-Delta (TETCO) with LED Status Indication				
Part Number	Price	Voltage	Timing	Function
TETCO-U030S-D52		24-28 VDC 50/60 Hz	3 to 30s	Star-Delta
TETCO-U030S-D61		110-130 VDC 50/60 Hz		
TETCO-U030S-D66		220-240 VDC 50/60 Hz		



TETCO-U030S-xxx


Note: Right side mounting

Timing Diagram




LED Off
 LED On
 Tm = Change over time

IEC Wiring Diagram



IEC Schematic Symbols





WEG CWC Series Miniature Contactors Accessories


Wiring Kits (Jumper Assemblies)

- Quick and easy assembly for wye-delta and reversing starters
- Allows assembly of WEG overload relay RW17 series overloads


Reversing Wiring Kit for Mini Contactors CWC07 to CWC016										
PartNumber	Price	Max Rated Operational Power of Three-Phase Motors 50/60 Hz kW [hp]						Rated Operational Current I_e AC-3 ($U_e \leq 440V$)	Mini Contactors	
		220V 230V	380V	400V 415V	440V	500V	660V 690V		K1 = K2	
ECC0-R		1.5 [2]	3 [4]	3 [4]	3.7 [5]	3.7 [5]	3 [4]	7	CWC07	
		2.2 [3]	4 [5.4]	4 [5.4]	4.5 [6]	4.5 [6]	4 [5.4]	9	CWC09	
		3 [4]	5.5 [7.5]	5.5 [7.5]	5.5 [7.5]	5.5 [7.5]	5.5 [7.5]	12	CWC012	
		4 [5.4]	7.5 [10]	7.5 [10]	7.5 [10]	7.5 [10]	7.5 [10]	16	CWC016	
Star-Delta Wiring Kit for Mini Contactors CWC07 to CWC016										
Part Number	Price	Max Rated Operational Power of Three-Phase Motors 50/60 Hz kW [hp]			Rated Operational Current I_e AC-3 ($U_e \leq 440V$)	Mini Contactors				
		220-230V	400-415V	660-690V		K1 = K2	K3			
ECC0-SD		3.7 [5]	5.5 [7.5]	5.5 [7.5]	12	CWC07	CWC07			
		3.7 [5]	7.5 [10]	9.2 [12.5]	18	CWC012				
		5.5 [7.5]	11 [15]	15 [20]	25	CWC016	CWC09			



ECC0-R Wiring Diagram



ECC0-SD Wiring Diagram





CWC Series Miniature Contactors Accessories




Mechanical Interlock Block and Latch Block

Mechanical Interlock Block and Latch Block			
Part Number	Price	Description	For Use With
BICO		Mechanical interlock, front mounted, use with any CWC07 through CWC016 series miniature contactor. Mechanically connects two CWC series mini contactors and prevents both contactors from being pulled in at the same time. For reversing contactors.	CWC07 CWC09 CWC012 CWC016
RMCO		Latch block, front mounted, use with any CWC07 through CWC016 series miniature contactor. Mechanically connects two CWC series mini contactors and enables one contactor to operate with a pulse input signal. Retention block for contactor.	



Note: Do not use BICO or RMCO accessory with mini contactors with low consumption DC coils.

Operation Description of Latched Block RMCO



- After a minimum pulse of 100ms on mini contactor's coil (K1), the RMCO will keep K1 contactor switched on;
- The mini contactor K1 will only return to rest position after miniature contactor's coil (K2) has been energized by a releasing pulse of 100ms;
- The mechanical latch only occurs when mini contactor (K1) is energized (ON).


Note: If RESET miniature contactor's coil (K2) remains energized, the latching of mini contactor (K1) is not enabled.





CWC Series Miniature Contactors Accessories - Dimensions

Dimensions


mm [in]




BFC0-xx, BFC4-xx, BFC025-xx



BICO, RMC0



RCC0-xxxx, VRC0-xxxx, DIC0-xxxx



TETC0-U030S-Dxx