
Bus Couplers PX-MOD

PX-MOD \$383.00



The PX-MOD Modbus RTU/ASCII Slave Bus Coupler allows connection of up to 64 terminals per assembly, 255 terminals total, in a Modbus RTU/ ASCII serial network. The PX-MOD communicates using high-level Modbus commands and supports 512 bytes of input data and 512 bytes of output data.

The PX-MOD includes one RS-485 D-sub 9-pin port that functions in half duplex for connection to a Modbus master.



PX-MOD I/O Bus Specifications		
Supply Power for I/O Bus	24VDC (-15%/+20%)	
Input Current from Power Supply	70mA + (total I/O bus current) / 4	
Recommended Fuse	10A Max	
I/O Bus Current Supply	1000mA Max	
Number of Bus Terminals Supported	64 per assembly, 255 w/ I/O Bus Expansion (based on power budget)	
Number of Discrete Inputs/ Outputs	1020 Inputs and 1020 Outputs with 255 terminals	
Number of Analog Inputs/Outputs	256 inputs and 256 outputs	
Maximum Number of Data Bytes*	* 512 Input Bytes and 512 Output Bytes	

^{*} Total number of terminals cannot exceed 512 input bytes and 512 output bytes.

PX-MOD Terminal Power Bus Specifications		
Supply Power for Terminal Bus 24 VAC/VDC		
Maximum Current	10A	
Number of Power Contacts	2 (+24 VAC/DC, 0V)	

PX-MOD Modbus Port Specifications		
Number of Stations 99		
Station Configuration Rotary Switches		
Protocol	Modbus RTU/ASCII (default = RTU)	
Data Transfer Rates	150, 300, 600, 1200, 2400, 4800, 9600, 19200, 38400 bau	
Maximum Cable Length	4000 ft. (1,200m)	
Connector Type	9-pin, D-Sub, RS-485	
Recommended Cable	24AWG, Shielded, Twisted Pair	

General Specifications		
Operating Temperature 32° to 131°F (0° to 55 °C)		
Storage Temperature	-13° to 185°F (-25° to 85 °C)	
Relative Humidity	5% to 95%, non-condensing	
Environment Air	No corrosive gases permitted	
Mounting/Orientation Restrictions 35mm DIN rail/None		
Vibration	Conforms to EN 60068-2-6	
Shock	Conforms to EN 60068-2-27	
Noise Immunity	Conforms to EN 61000-6-2	
Protection Class	IP20	
Weight	100g (3.5 oz)	
Dimensions (WxHxD)	44mm x 100mm x 66.4 mm (1.73 in x 3.94 in x 2.61 in)	
Agency Approvals*	UL/cUL File No. E157382, CE	

^{*} To obtain the most current agency approval information, see the Agency Approval Checklist section on the specific part number's web page.





Hot-Swapping Information

Note: This device cannot be Hot Swapped.

Bus Couplers PX-MOD


Configuration Port




The Service Port connector is located under the flip-cover shown. This port is used for communication with the software configuration tool. The software configuration tool autoconfigures the Modbus addresses of the I/O terminals and the interface allows the user to:

- Run the configurator View the configured Modbus addresses Modify the baud rate
- Change the Modbus offset Reboot the coupler Disable or modify Watchdog timer Requires cable PX-USB-232, with a USB type A connector for the PC and a 4-pin custom micro connector for the Bus Coupler. Works with PX-CFGSW configuration software.





LED Descriptions			
LED	Status: ON	Status: OFF	
Green LED 1: WD	Watchdog is active	Watchdog error	
Green LED 2: RX	Data being received No data being received		
Green LED 3: TX	Data being transmitted No data being transmitted		
Red LED 4: ERROR	Data Error, communications with the master device has been lost		
Green LED 5: Us	Bus Coupler power on Bus Coupler power off		
Green LED 6: Up	Terminal power on Terminal power off		
Green LED 7: I/O RUN	I/O bus data active Watchdog-timer overflow		
Red LED 8: I/O ERR	I/O bus error, blinking code	No I/O bus error	



Address Selection -Rotary Switches

The Modbus node address for the <u>PX-MOD</u> is set using both rotary switches on the front of the Coupler. The address is configured within the 01 to 99 range. The configured value of 00 is reserved for programming and configuration.

The lower rotary switch is used to set the tens digit (x10) of the node address. The upper rotary switch is used to set the ones digit (x1) of the node address. The switch address is accepted only when power is cycled. The example shown is configured for a node address of 21.

Bus Couplers PX-MOD

System Considerations

The <u>PX-MOD</u> performs as a Modbus RTU/ASCII slave in a Modbus network. Communication to the master is via a 9-pin D-sub RS-485 port. The maximum distance from the master to the PX-MOD is 4000 feet (1200 meters) using 24 AWG shielded, twisted pair. Termination resistors are required at the beginning and end of the network. It is highly recommended that a dedicated network be used for the Protos X system.

The PX-MOD Bus Coupler supports up to 64 terminals per assembly, 255 with Bus Expansion Couplers. A minimal assembly consists of a PX-MOD Bus Coupler, I/O Terminals and a Bus End Terminal.


An I/O Bus, powered through the Bus Coupler, provides data communication across the terminal assembly via six contacts located on the side walls of the terminals. A Terminal Power Bus provides power for the I/O terminals via two power contacts. A power source of 24VAC or 24VDC must be connected to the Bus Coupler from an external supply.


If additional 24VDC supply is required for terminal wiring, eight points of 24VDC power can be distributed from the Terminal Power Bus using a Power Distribution Terminal (PX-949). This terminal must be mounted to the right of a terminal that passes 24VDC on the power bus. Both I/O Bus communication and terminal bus power are passed through to adjoining terminals.

For expansion beyond a 64-terminal assembly, a Bus Expansion End Terminal (PX-902) is used in place of a standard Bus End Terminal (PX-901). A Bus Expansion Coupler Terminal (PX-903) is used at each expansion assembly in place of a PX-MOD Bus Coupler. Up to 31 Expansion couplers can be used in a group of assemblies. Connection is made between the Expansion Coupler Terminals via standard RJ45 Ethernet patch cable.

It is important to stay within the following three specifications:.


- 1. Do not exceed the total number of 64 Terminals allowed per Assembly.
- 2. Do not exceed the total number of 512 Input Bytes and 512 Output Bytes.
- 3. Do not exceed the Coupler I/O Bus Power Budget of 1000mA as there is no internal current protection.





Bus Couplers - PX-MOD

PX-MOD Wiring Connections



Power Budget Planning

Managing Power Resources

When determining the types and quantity of terminals you will be using, it is important to remember there is a defined amount of I/O Bus Current supplied from the Bus Coupler. There are also defined limits for each external source.

The chart on the next page indicates the power supplied and used by each Protos X component. The chart below shows an example of how to calculate the power used by your particular system. These charts should make it easy for you to determine if the devices you have chosen will operate within the power budget of your system configuration.

If the I/O terminals you have chosen exceed the maximum power available from the Bus Coupler, you may be able to resolve the problem by using expansion terminals.

Power Budget Example

The example below shows how to calculate the power budget for a typical ProtosX system. This example is constructed using a PX-MOD Bus Coupler and six I/O Terminals. It is recommended you construct a similar table for your system. Follow the steps below to determine your power budget.

Α	Column 1	Column 2	Column 3
	Terminal	Terminal Type	I/O Bus (from Coupler)
В	CURRENT SUPPLIED		
	PX-MOD	Bus Coupler	1000mA
C	CURRENT REQUIRED		
	PX-144 4 pt DC Discrete Input PX-172-1 2 pt AC Discrete Input PX-322-1 2 ch RTD Input PX-312 2 ch DC Analog Input PX-244-1 4 pt DC Discrete Output PX-412 2 ch DC Analog Output		5mA 3mA 60mA 65mA 9mA 75mA
D	Maximum Current Required		217mA
Ε	Remaining Current Available		783mA

- 1. Using a chart similar to this one, fill in columns 1 and 2.
- Using the tables on the next page enter the current supplied and current used by each device (column 3).
- 3. Add together the current used by the system (row C) for column 3 and put the total in the row labeled "Maximum Current Required" (row D).
- 4. Subtract the calculated "Maximum Current Required" (row D), from the "Current Supplied" and place the difference in the row labeled "Remaining Current Available" (row E).
- If "Maximum Current Required" is greater than "Current Supplied" in column 3, the power budget will be exceeded. It will be unsafe to use this configuration, and you will need to restructure your I/O configuration.

Power Requirements

Power Supplied and Consumed

These tables show the amount of power supplied by each of the Bus Couplers and the amount of power consumed by each I/O device. The Power Consumed chart lists how much power is drawn from the I/O Bus, Terminal Power Bus (externally supplied) and from the Load (when using output terminals). Use this information when calculating the power budget for your system.

Power Supplied		
Device 5V(mA) I/O Bus Supply		
Coupler		
PX-MOD 1000 Max		
PX-TCP1	1000 Max	
PX-TCP2	1750 Max	
PX-EIP1	1000 Max	
Bus Expansion Coupler		
<u>PX-903</u>	400 Max	

Power Consumed			
Device	5V(mA) from I/O Bus	(mA) from Terminal Power Bus	(mA) from Load
	Discrete II	nput Terminals	
PX-144	5	5	
PX-148	5	2 (plus load)	
PX-149	20	N/A	N/A
PX-172-1	3	6	
PX-172-2	3	6	
	Discrete O	utput Terminals	
PX-244-1	9		30
PX-244-2	9	NI/A	30
PX-248	18	N/A	60 (plus load)
PX-249	45		35 (plus load)
	Analog In	put Terminals	
PX-302	60	N/A	
PX-304	85	Load	
PX-308	105	Load	NI/A
PX-312	65	N/A	N/A
PX-314	100	N/A	
PX-318	140	N/A	
	RTD/Thermocou	ıple Input Terminals	
PX-322-1	60		
PX-324-1	60		
PX-332-J	65	NI/A	
PX-334-J	75	N/A	N/A
PX-332-K	65		
PX-334-K	75		
	Analog Ou	tput Terminals	
PX-402	60		50 (plus load)
PX-404	20		60 (plus load)
PX-408	25	1	50 (plus load)
PX-412	75	N/A	50 (plus load)
PX-414	75	-	50 (plus load)
PX-418	20	1	20
	Relay Out	put Terminals	
PX-272-1	10	ON resistance max 100mV	
PX-272-2	80	(plus load)	N/A
	Combination	In/Out Terminals	
PX-549	25 (additional 3mA for inputs)	15 (plus load)	N/A

System Installation and Removal


Bus Coupler and Bus Terminal Installation

Bus Coupler Installation:

 Attach a Bus Coupler by snapping it onto 35mm DIN rail and securing it into position using the DIN rail locking wheel (where applicable) located on the left side of the coupler.


Bus Terminal Installation:

- To add a bus terminal, insert unit onto right side of Bus Coupler using the tongue and groove at the top and bottom of the unit, pressing gently until it snaps onto the DIN rail.
- A proper connection cannot be made by sliding the units together on the DIN rail.
 When correctly installed, no significant gap can be seen between the attached units. Bus connection is made through the six slide contacts located on the upper right side of the units. Add up to 64 bus terminals per Bus Coupler, including a bus end terminal.



Wiring Connections

 Wire connection is made through a spring clamp style terminal. This terminal is designed for a single-conductor solid or stranded wire. Wire connection is made by firmly pushing the screwdriver into the screwdriver slot, inserting the wire into the wire slot and removing the screwdriver, locking the wire into position.





Wiring Specifications		
Connection Type Spring Clamp Terminals		
Wire Gauge	28-14 AWG (0.08-2.5 mm2)	
Screwdriver Width 2.5 mm (0.10 in) such as P/N TW-SD-MSL-2		
Wire Stripping Length	8mm	

^{*} For Thermocouple terminals, thermocouple extension wire is recommended

Removing Bus Coupler and Bus Terminals

 A locking mechanism prevents individual units from being pulled off. For bus terminal removal, pull the orange DIN rail release tab firmly to unlatch the unit from the rail. If attached to other terminal units, slide unit forward until released. For Bus Couplers with locking wheels, release the DIN rail locking wheel, then pull firmly on DIN rail release tab.

Where applicable, rotate Locking Wheel to unlock Bus Coupler




Firmly pull DIN Rail Release Tab to unlatch unit from rail.


Installation Considerations

Terminal Dimensions and Spacing Requirements

Use the following diagrams to make sure the Protos X system can be installed in your application. Protos X terminals require 35mm DIN rail for mounting; there are no orientation restrictions.

To ensure proper airflow for cooling purposes, units should be spaced, at a minimum, as shown. It is also important to check the Protos X dimensions against the conditions required for your application.





Installation Considerations

Terminal Types

