



P/N: INST-GEN-PMKG-CLP
GENESIS POLE MOUNTING KIT


Installation Instructions:

The kit consists of the following components

- Item A) Strut Rails – QTY (2)
- Item B) Strut Pipe Clamps (Halves, B' & B'')-QTY (2)
- Item C) Fender Washer, 1/4" – QTY (4)
- Item D) Pan Head Screws, 1/4-20 X 3/4" Long – QTY (4)
- Item E) Nylok Nut, 1/4-20 – QTY (4)

- Item F) Hex Cap Screws, 5/16-18 X 1-1/4" long– QTY (2)
- Item G) Square Nuts, 5/16-18 – QTY (2)

- 1) Insert Pipe Clamp halves (B' & B'') into Strut Rails (A) as shown. Do not tighten (x2).
- 2) Install Pan Head Screws (D) through holes in Enclosure Base (x4). Attach Strut Rail (A) to Enclosure Base securing with Fender Washers (C) & Nylok Nuts (E). Torque to 32 in-lbs Max.
- 3) Straddle the Pipe Clamp halves (B' & B'') around the Pole (not shown), position & align for assembly (x4).
- 4) Secure Pipe Clamps to Pole with 5/16-18 Cap Screws (F) and 5/16 Nuts (G), (x2). Torque to 100 in-lbs Max.



Integra Enclosures, Inc.

7750 Tyler Blvd / Mentor, OH 44060 / Voice 440-269-8155 / Fax 440-269-4977 / www.integraenclosures.com (INST-GEN-PMKG-CLP_Rev_A)



P/N: INST-GEN-PMKG-CLP
GENESIS POLE MOUNTING KIT


Installation Instructions:

The kit consists of the following components

- Item A) Strut Rails – QTY (2)
- Item B) Strut Pipe Clamps (Halves, B' & B'')-QTY (2)
- Item C) Fender Washer, 1/4" – QTY (4)
- Item D) Pan Head Screws, 1/4-20 X 3/4" Long – QTY (4)
- Item E) Nylok Nut, 1/4-20 – QTY (4)

- Item F) Hex Cap Screws, 5/16-18 X 1-1/4" long– QTY (2)
- Item G) Square Nuts, 5/16-18 – QTY (2)

- 1) Insert Pipe Clamp halves (B' & B'') into Strut Rails (A) as shown. Do not tighten (x2).
- 2) Install Pan Head Screws (D) through holes in Enclosure Base (x4). Attach Strut Rail (A) to Enclosure Base securing with Fender Washers (C) & Nylok Nuts (E). Torque to 32 in-lbs Max.
- 3) Straddle the Pipe Clamp halves (B' & B'') around the Pole (not shown), position & align for assembly (x4).
- 4) Secure Pipe Clamps to Pole with 5/16-18 Cap Screws (F) and 5/16 Nuts (G), (x2). Torque to 100 in-lbs Max.



Integra Enclosures, Inc.

7750 Tyler Blvd / Mentor, OH 44060 / Voice 440-269-8155 / Fax 440-269-4977 / www.integraenclosures.com (INST-GEN-PMKG-CLP_Rev_A)