## 1-800-633-0405 Shutters and Adapters

## Shutters for M18 (18mm) Through-beam Sensors (SSE / SSR)

• Reduces the emitted beam, allowing the detection of small targets

• Shutter consists of an aluminum cap and aperture with an O-ring and glass lens, which can screw onto the optical head of either the emitter or receiver

Sensing Distance (When Used with SSE / SSR Model Photoelectric Switches)						
Model	<u>stos1</u>	<u>stos2</u>	<u>stos3</u>	<u>stos4</u>	<u>ST0S6</u>	STOS8
Price	Retired	Retired	Retired	Retired	Retired	Retired
Ø x shutter (mm)	1	2	3	4	6	8
Distance (m) Object (mm)	N/A	N/A	N/A	1.5 2	3.5 3	6.5 4

Table shows sensing distance and minimal detectable object.

Shutter Accessory for QM Series Sensors				
Part Number	Price	Drawing Link	Description	Weight [lb]
<u>STQM0</u>	\$6un:	<u>PDF</u>	Micro Detectors shutter, plastic. Package of 2. For use with through beam QM series photoelectric sensors. Vertical and horizontal diaphragms (0.5, 1, 2mm) included.	0.1

Shutter STQM0 Sensing Distances						
Shutter Size	0.5 mm	1mm	2mm			
Maximum Sensing Distance	1.5 m	2 m	4.5 m			
Minimum Detectable Object Diameter	0.8 mm	1.5 mm	2.5 mm			

Note: With shutters on emitter and receiver in same vertical or horizontal orientation.


## Right-angle M18 (18 mm) Beam Adapter

For use with M18 retroreflective and through-beam photoelectric switches (not for use with diffuse reflection sensors). Allows 90° light detection using an internal mirror set at 45° to the optical axis. Sensitivity loss is about 20-30%.

Beam Adapters				
Part Number	Part Number Price Description		Weight [lb]	
<u>ST03</u>	\$;04b!:	Micro Detectors right-angle beam adapter, for use with 18mm sensors (except diffuse reflection models), mirror allows 90 degree light detection.	0.06	


**Dimensions** mm [inches]

ø16 [ø0.63]





**Dimensions** mm [inches]





<u>ST03</u>