

Industrial Gloves



General purpose industrial work gloves

- For basic assembly and chore use
- Close fit for excellent dexterity
- Quality nylon yarn for stretch
- Polyurethane coated for grip
- Cuff color-coded by size

TTP-NYPU-11

General Purpose Industrial Gloves Specifications				
Part Number	TTP-NYPU-6	TTP-NYPU-7	TTP-NYPU-8	TTP-NYPU-11
Price				
Pairs/package	6	6	6	6
Size	6 (XS)	7 (S)	8 (M)	11 (XXL)
Glove Color	Black	Black	Black	Black
Cuff Color	Pink	Yellow	Blue	Black
Material				
Glove	Nylon			
Coating	Polyurethane			
Gauge	13			
Cut Resistance				
Cut Test	Not cut resistant			



Anti-static industrial work gloves

- Protect hand and product from electrostatic build-up
- Nylon and Resi-stat yarn blend for fit and static dissipation
- Maximum dexterity
- Pre-washed
- Ambidextrous
- Cuff color-coded by size

TTP-ESD-10

Anti-Static Industrial Gloves Specifications						
Part Number	TTP-ESD-6	TTP-ESD-7	TTP-ESD-8	TTP-ESD-9	TTP-ESD-10	TTP-ESD-11
Price						
Pairs/package	6	6	6	6	6	6
Size	6 (XS)	7 (S)	8 (M)	9 (L)	10 (XL)	11 (XXL)
Glove Color	White and gray blend	White and gray blend	White and gray blend	White and gray blend	White and gray blend	White and gray blend
Cuff Color	Yellow	Blue	Green	Red	Black	Brown
Material						
Glove	Carbon fiber nylon knit with Resi-stat yarn					
Coating	None					
Gauge	13					
Electro-static Dissipative Exposure						
Test Compliance	ANSI/ESD STM2.1 Resistance test method for electrostatic discharge protective garments. 8 ¹⁰ Ω resistivity					

Industrial Gloves



Industrial Work Gloves Selection

- General purpose
- Anti-static, pre-washed
- Puncture and cut resistant
- Puncture resistant with knuckle padding
- Cut-resistant, polyurethane-coated or rubber-coated
- Arc flash-rated, cut resistant, full leather
- Mechanic style, cowhide leather palm
- Cut resistant sleeves

Sizing Chart					
6	7	8	9	10	11
X-Small	Small	Medium	Large	X-Large	2X-Large



Measure around your hand across the widest part of your palm.

The reading in inches is an estimate of the equivalent glove size. If your reading is between sizes, order the larger size.